

KERN KS-A01

KERN

Rechargeable battery pack external, operating time up to 30 h without backlight, charging time approx. 10 h



Dimensions packaging (W×D×H)	150×106×85 mm
Shipping method	Parcel service
Net weight approx.	0,45 kg
Gross weight approx.	0,55 kg
Shipping weight	0,51 kg

Product information

GTIN/EAN number	4045761208537
-----------------	---------------

Pictograms

STANDARD



Category

Brand	KERN
Product category	Balance
Product group	Rechargeable battery

Power Supply

Supplied power supply	Power supply unit
-----------------------	-------------------

Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
---	------------------------

Plug-in power supply / adapter for countries - optional	EURO UK US CH
---	------------------------

Input voltage power supply / power [Max]	9 V, 2 A
--	----------

Power socket for mains adapter	Hollow plug, inside minus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 9,5 mm
--------------------------------	---

Battery / accumulator type	Li-Po (Li-Ion)
----------------------------	----------------

Battery operating time	40 h
------------------------	------

Battery capacity	12.800 mAh
------------------	------------

Battery voltage	9 V
-----------------	-----

Battery capacity (Wh)	48,64 Wh
-----------------------	----------

Battery – Tests passed UN 38.3	✓
--------------------------------	---

Rechargeable battery charging time	10 h
------------------------------------	------

Rechargeable battery optional	Rchrg. battery optional
-------------------------------	-------------------------

Packing & Shipping

Delivery time	1 d
---------------	-----