

# KERN KXP30V20M

Edelstahl-Wägeplatte



## Measuring system

Readout [d]:	1 g
Resolution (non verifiable):	30000
Weighing range [Max]:	30 kg

## Technical data about verification

Minimum load [Min]:	200 g
Verification by KERN possible:	yes
Verification value [e]:	5 g   10 g

## Service

Adjustment at the location of installation: 961-248

DAkkS Certificate:	963-128
Verification:	965-228

## Category

Brand:	KERN
Category:	Platforms
Product Group:	Platform

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	500 x 410 x 225 mm
Gross weight:	9,200 kg
Net weight:	7,500 kg
Shipping method:	Parcel service

## Construction

Cable length:	3 m
Dimensions of weighing plate (WxDxH):	400 x 300 x 89 mm
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (WxD):	400 x 300 mm