

KERN KXP60V20M

Edelstahl-Wägeplatte



Measuring system

Readout [d]:	2 g
Resolution (non verifiable):	30000
Weighing range [Max]:	60 kg

Technical data about verification

Minimum load [Min]:	400 g
Verification by KERN possible:	yes
Verification value [e]:	10 g 20 g

Service

Adjustment at the location of installation: 961-249

DAkkS Certificate:	963-129
Verification:	965-229

Category

Brand:	KERN
Category:	Platforms
Product Group:	Platform

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	630 x 495 x 210 mm
Gross weight:	12,900 kg
Net weight:	10,900 kg
Shipping method:	Parcel service

Construction

Cable length:	3 m
Dimensions of weighing plate (WxDxH):	400 x 300 x 89 mm
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (WxD):	400 x 300 mm