

KERN MPD200K-1EM

Professionelle Step-On-Personenwaage mit Eich- und Medizinzulassung



Service

Adjustment at the location of installation: 961-249

DAkkS Certificate: 963-129

Verification: 965-129

Category

Brand: KERN

Category: Balances

Product Group: Personal floor scale

Packaging & shipping

Delivery: 24 h

Dimensions packaging (WxDxH): 550 x 440 x 200 mm

Gross weight: 10,500 kg

Net weight: 8,700 kg

Shipping method: Parcel service

Construction

Casing material: Steel lacquered

Dimensions of display device (WxDxH): 200 x 55 x 128 mm

Dimensions of weighing plate (WxDxH): 365 x 360 x 80 mm

Level indicator: yes

Material weighing plate: Plastic

Overall dimensions mounted (WxDxH): 365 x 490 x 120 mm

Revolving screw feet: yes

Measuring system

Adjustment options: External calibration

Linearity: 200 g

Readout [d]: 200 g

Recommended adjusting weight: 200 kg (M1)

Reproducibility: 200 g

Resolution: 1250

Warm up time: 10 min

Weighing range [Max]: 250 kg

Weighing system: Strain gauge

Weighing units: kg

Display

Display digit height: 2,500 cm

Technical data about verification

Minimum load [Min]: 4 kg

Periodic Verification for Italy: 969-112

Verification approval conforming to 2014/31/EU: yes

Verification by KERN possible: yes

Verification class: III

Verification value [e]: 200 g

Environmental conditions

Maximum humidity: 80 %

Maximum operating temperature: 40 °C

Minimum ambient temperature: -10 °C

Power supply

Operating time: 20 h