

KERN PNS 12000-1

Der neue Standard im Labor mit dem robusten Stimmgabel-Wägesystem



Measuring system

Adjustment options:	External calibration
Linearity:	200 mg
n/a:	200 g
Readout [d]:	100 mg
Recommended adjusting weight:	12 kg (F1)
Reproducibility:	100 mg
Resolution:	120000
Stabilisation time:	3 s
Tare range:	12 kg
Warm up time:	2 h
Weighing range [Max]:	12 kg
Weighing units:	ct dwt g lb mo oz ozt tl (HK) tl (Singap. Malays) tl (Tw) tol

Display

Display digit height:	1,650 cm
-----------------------	----------

Counting

Counting resolution:	120000
Minimum piece weight at piece counting (Laboratory):	100 mg
Minimum piece weight at piece counting (Normal):	1 g

Functions

Counting function:	yes
Percentage determination:	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	5 °C

Power supply

Input voltage:	220 V - 240 V AC 50 Hz
n/a:	CH EURO UK US

n/a:	Mains adapter external
------	------------------------

Service

DAkkS Certificate:	963-128
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	325 x 410 x 220 mm
Gross weight:	5,200 kg
Net weight:	2,600 kg
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	196 x 293 x 89 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (WxD):	190 x 190 mm