

# KERN OBB-A 139 1

Infinity PH-Plan-objective 20x

**KERN**



## Pictograms

### STANDARD



## Category

|                  |                    |
|------------------|--------------------|
| Brand            | Optics             |
| Product category | Optical Instrument |
| Product group    | PH-Objective       |

## Construction

|             |   |
|-------------|---|
| Anti fungus | ✓ |
|-------------|---|

## Objective

|                            |               |
|----------------------------|---------------|
| Objective magnification    | 20x           |
| Objective quality          | Infinity Plan |
| Numerical Aperture         | 0,4           |
| Objective working distance | 2,41 mm       |

## Environmental conditions

|                           |       |
|---------------------------|-------|
| Storage temperature [Min] | -5 °C |
| Storage temperature [Max] | 40 °C |

## Packing & Shipping

|                              |                |
|------------------------------|----------------|
| Delivery time                | 1 d            |
| Dimensions packaging (W×D×H) | 65×40×40 mm    |
| Shipping method              | Parcel service |
| Net weight approx.           | 0,30 kg        |
| Gross weight approx.         | 0,60 kg        |
| Shipping weight              | 0,6 kg         |

## Product information

|                      |                          |
|----------------------|--------------------------|
| GTIN/EAN number      | 4045761176171            |
| REACH classification | no prohibited substances |