


1-800-383-7323 USA/CAN www.energizer.com

ENERGIZER A91





Industry Standard Dimensions



Specifications

Classification: Alkaline

Chemical System: Zinc-Manganese Dioxide (Zn/MnO ₂)

No added mercury or cadmium

Designation: ANSI-15A, IEC-LR6

Nominal Voltage: 1.5 volts

Operating Temp: -18°C to 55°C (0°F to 130°F)


Typical Weight: 23.0 grams (0.8 oz.)

Typical Volume: 8.1 cubic centimeters (0.5 cubic inch) **Jacket:** Plastic Label

Shelf Life: 10 years at 21°C **Terminal:** Flat Contact

Performance Comparison


A91 vs. Typical Carbon Zinc (AA) at 21°C



Industry Standard Testing Protocol

Device Selection Guide:

Battery Selection Indicator



This data sheet contains typical information specific to products manufactured at the time of its publication.

©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.

Form No. EBC - 1189I Page 1 of 1