

Nokia 3310



Main color options*:

Orange
Blue
Yellow,
Grey,

Sales package*:

Device
Nokia MicroUSB charger
Charging / data cable
Quick guide

hmd.

The Home of Nokia Phones

Networks	GSM 900/1800(EU) (QB SS LTA not in scope)
OS	S30+
CPU	MTK 6260C
Storage	16MB internal user memory with microSD-slot (up to 32GB support)
Form factor	ITUT
Display	2.4" QVGA clear black.
Camera	2Mpxl with LED Flash
Connectivity/ Sensors	Micro USB (USB 2.0), 3.5mm AV jack, Bluetooth
Battery	Removable 1200 mAh battery
Talk and standby time (estimates)	Maximum 2G talk time: up to 24hrs Maximum 2G standby time: up to 1 month Music playback time:
Audio	FM Radio, MP3 player.
Dimensions	115.6*51*12.75mm