

Product MD 302 R

3 mm LED indicator
color red

product-catalog	3 mm LED indicator
color	red
part no.	MD 302 R
forward voltage [V]	2.1
wavelength [nm]	700
rec. mounting hole Ø [mm]	4.4
panel thickness [mm]	1 .. 2
operating temperature [°C]	-25 .. +80
storage temperature [°C]	-30 .. +85

chip construction	GaP
forward current max. [mA]	25
reverse voltage max. [V]	4
luminous intensity typ. [mcd]	6 at 15 mA

Low cost LED indicator with ribbed nylon body for easy front panel mounting;

min. 22 mm pins, without resistor

note

- all dimension are in millimeter
- tolerance is ± 0.25 mm unless otherwise noted
- specifications are subject to change without notice
- version 1.0

