

Product MD 567 Y

5 mm LED indicator
color yellow

product-catalog	5 mm LED indicator
color	yellow
part no	MD 557 Y
forward voltage typ. [V]	2.1
wavelength [nm]	585
rec. mounting hole Ø [mm]	6.35
panel thickness [mm]	1 .. 3
operating temperature [°C]	-25 .. +80
storage temperature [°C]	-30 .. +85

chip construction	GaAsP
forward current max. [mA]	25
reverse voltage max. [V]	4
luminous intensity typ. [mcd]	30

Low cost LED indicator with ribbed nylon body for easy front panel mounting

150 mm PVC leads *, AWG 26, without resistor, cathode lead = blue

* for special lead length add appendix -Lxxx (xxx length in mm) to standard P/N

note

- all dimension are in millimeter
- tolerance is ± 0.25 mm unless otherwise noted
- specifications are subject to change without notice
- version 1.0

