



Datasheet

Item no. 1564534

V1 1021 01 en

USB type-A female socket PCB solder pin terminal connector

Specification

USB type: 2.0 type A Female

Dimension: 32.3 x 16 x 8 mm (max.)


Voltage rating: 5 V/ DC Current rating: 2 A max.


Insulation resistance: $100M\Omega$ min. Contact resistance: $30m\Omega$ max.


Withstand voltage: 100V/AC, for 1min. Operating temperature: -30 ~ 80°C Operating humidity: >85%RH


Durability: >1000 cycles











This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data represent the technical status at the time of printing. Changes in technology and equipment reserved.