

Item no.:

1567788 - Black 1567793 - Blue 1564655 - Brown 1570358 - Green 1567789 - Grey
1567790- Orange 1565350 - Red 1567791 - Violet 1565351 - White 1564656 - Yellow



Data Sheet

LIFY high flex cable 0.05 mm²

Jacket, outer dimension.....	PVC 0.8 mm
No. of conductors.....	10 x 0.08 mm
Cross section of conductor.....	0.05 mm ²
Length.....	100 meters
Conductor material	copper
Insulation material (with thickness).....	PVC 0.27 mm
Core diameter.....	0.26 mm
Insulation resistance.....	Min 200M ohm x km
Conductor resistance.....	Max 430 Ω / KM
Maximum dielectric strength.....	800 V / AC
Operating & storage temperature range.....	-20 to +70 °C
Rated voltage.....	48 V / DC
Rated current.....	0.4 A
Conductor structure.....	Twisted