

Data Sheet

6.35 mm audio jack plug, straight 2 pins



Technical data

Colour: silver

No. of pins: 2

Audio Channel: mono

Contact plated: Nickel

Connection: Soldering

Category: 6.35mm

Connector type: Plug, straight

Mating cycles: > 3000

Dimension: 66.4*11.4*11.4 mm

Tolerance: ± 1 mm

Housing material & coating: zinc alloy/nickel plating, black

Contact resistance: ≤ 10 m Ω

Mechanical life(cycles): >1000 cycles

Cable diameter can be used: 3.5-8.0 mm

Withstand voltage: 0.5kV dc