

Datasheet

Item no. 1566396 1566392 1566397 1564985 1564984
 1566393 1566395 1570067 1564983 1566394
 1571979 1566391 1570069

V1_07262018_01_en

Neon Lamp Series

B/N	Model no.	Colour	Lamp Size	Lead Wire (mm)		Break down (V)		Design Current (mA)	Series Resistor		Life (h)
			ø x L (mm)	ø (mm) ± 0.02	length (mm) ± 1	AC	DC		110-120VAC	220-250VAC	
1566396	NE-2 4x10/30mm	Standard Brightness	4 x 10	0.35	30	65	90	0.5	100	330	25000
1566392	NE-2 5x12/30mm	Standard Brightness	5 x 12	0.4	30	65	90	0.5	100	330	25000
1566397	NE-2 6x16/30mm	Standard Brightness	6 x 16	0.4	30	65	90	0.5	100	330	25000
1564985	NE-2 6x22/30mm	Standard Brightness	6 x 22	0.4	30	65	90	0.5	100	330	25000
1564984	NE-2UH 4x10/30mm	Ultra Brightness	4 x 10	0.35	30	95	135	1.5	33	100	25000
1566393	NE-2UH 5x12/30mm	Ultra Brightness	5 X 12	0.4	30	95	135	1.5	33	100	15000
1566395	NE-2UH 6x16/30mm	Ultra Brightness	6 X 16	0.4	30	95	135	2.0	22	68	15000
1570067	NE-2UH 6x18/30mm	Ultra Brightness	6 X 18	0.4	30	95	135	2.0	22	68	15000
1564983	NE-2G 4x10/30mm	Green Brightness	4 x 10	0.35	30	85	120	0.5	100	330	20000
1566394	NE-2G 6x16/30mm	Green Brightness	6 x 16	0.4	30	85	120	1.0	47	150	15000
1571979	NE-2W 4x10/30mm	White Brightness	4 x 10	0.35	30	85	120	0.5	100	330	15000
1566391	NE-2W 5x12/30mm	White Brightness	5 x 12	0.4	30	85	120	0.7	82	220	15000
1570069	NE-2B 4x10/30mm	Blue Brightness	4 x 10	0.35	30	85	120	0.5	100	330	10000