

Data Sheet

PVC twin cable / Installation cable Datasheet



The Application:
Rated Voltage.48V
splittable cable

Temperature range min. -20° C
Temperature range max. 70° C

B/N	1566632	1571331	1570890	1565082
Item No.	PVC twin cable	PVC twin cable	PVC twin cable	PVC twin cable
Jacker, outer dimension	PVC 4.5X2.3mm	PVC 4.5X2.3mm	PVC 4.5X2.3mm	PVC 4.5X2.3mm
AWG	19	19	19	19
No. of conductors	2 x 0.75 sqmm	2 x 0.75 sqmm	2 x 0.75 sqmm	2 x 0.75 sqmm
CCA strand per conductor	27 x 0.19 mm	27 x 0.19 mm	27 x 0.19 mm	27 x 0.19 mm
color	white	white	black	black
capac cond	140 pF	140 pF	140 pF	140 pF
Packaging	20 meter spool	10 meter spool	20 meter spool	10 meter spool

B/N	1565083	1570679	1566633
Item No.	Installation cable	Installation cable	Installation cable
Jacker, outer dimension	PVC 4.5X2.3mm	PVC 4.5X2.3mm	PVC 4.5X2.3mm
AWG	19	19	19
No. of conductors	2 x 0.75 sqmm	2 x 0.75 sqmm	2 x 0.75 sqmm
CCA strand per conductor	27 x 0.19 mm	27 x 0.19 mm	27 x 0.19 mm
color	white	white	black
capac cond	140 pF	140 pF	140 pF
Packaging	50 meter spool	50 meter spool	50 meter spool