

Datasheet

Item no. 1565175

V1_0917_01_en

Waterproof DC fan, 12V, 0.09A

Model: RD8025B12L

Specifications

1、 Mechanical	
1-1、 External dimension	80*80*25mm
1-2、 Weight	54g
1-3、 Bearing	Two Ball bearing
2、 Electrical characteristics (in free air at rated voltage)	
2-1、 Rated voltage	12V
2-2、 Rated current	0.09±10%A
2-3、 Rated input power	1.08±10%W
3、 Efficiency	
3-1、 Rated speed(range)	2400RPM±10%
3-2、 Maximum air flow	25.30CFM
3-3、 Maximum static air pressure	2.44mm-H2O
4、 Characteristics	
4-1、 Operating voltage range	7.5V~13.8V
4-2、 Starting voltage	7.5(ON/OFF)
4-3、 Locked current	0.14A(Reference)
4-4、 Operating temperature	-10℃~+70℃
4-5、 Storage temperature	-30℃~+85℃
4-6、 Water Level	IP58
4-7、 Environment humidity	10%(RH)45℃ for 24 hours & 98% (RH) 45℃ for 24 hours
4-8、 Insulation resistance	At least 10MΩ at 500 VDC between housing and both lead wires
4-9、 Dielectric strength	Withstand 500 VAC 1 minute 1mA between housing and both lead wires
4-10、 MTBF: 50,000 hours	
Life expectancy:50,000Hours continuous operation at rated voltage and normal temperature & humidity	

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

© Copyright 2017 by Conrad Electronic SE.