


Data Sheet

PVC Insulated Twin Wire



Technical & Specification

Cross-section	2 x 0.14mm ²
External Dia.	1.3 x 2.6mm ±0.1
Construction	28 x ø0.08mm
Material:	
Conductor	Cu blank
Insulator	PVC
Jacket Color	Black+Red Yellow+Brown
Dielectric strength	0.5kv/ 1 minute
Rated voltage	75VDC / 50VAC
Conductor Resistance	142Ω/KM at 20°C
Insulator Resistance	15MΩ/KM at 20°C
Flame Class	94V-2
Operating Temperature	-10 ~ 70°C