

Item no.: 1567809, 1570361, 1564659, 1567811, 1567815, 1567812, 1564661, 1567810, 1567814, 1564660, 1567813, 1572458, 1572467, 1572461, 1572460, 1572466, 1572462, 1572464, 1572459, 1572465, 1571570, 1572463, 1564657, 1565353, 1567796, 1567795, 1567801, 1565352, 1567799, 1567794, 1567800, 1567797, 1567798, 1567802, 1564658, 1570359, 1567804, 1570360, 1567807, 1567803, 1567808, 1567805, 1567806

Data Sheet

LIFY Highflex Cable 0.25 mm², 25M



Technical data

Jacker, outer dimension: PVC 1.4mm

No. of conductors: 50 x 0.08mm

Strand per conductor: 0.25 sqmm

Color: black/red/green/brown/white/grey/yellow/orange/violet/green-yellow/blue

Packaging: blue spool

Length: 10/25/50/100 meter

Conductor material: copper

Insulation material (with thickness): PVC 0.42mm

Core diameter: 0.56mm

Insulation resistance: Min 200M ohm x km

Conductor resistance: Max 85Ω/KM

Maximum dielectric strength: 1200V / AC

Temperature range: -20 to +70 C

Rated voltage: 48V

Rated current: 2A

Conductor structure: Twisted