

Item no.:

1565366 - Black    1571021 - Blue    1564667 - Brown    1567847 - Green    1564668 - Grey  
1564669 - Orange    1572469 - Red    1571020 - Violet    1567848 - White    1567849 - Yellow  
1567850 - Green/Yellow



## Data Sheet

---

### LIFY high flex cable 0.75 mm<sup>2</sup>

Jacket, outer dimension.....	PVC 2.2 mm
No. of conductors.....	96 x 0.1 mm
Cross section of conductor.....	0.75 mm <sup>2</sup>
Length.....	25 meters
Conductor material .....	copper
Insulation material (with thickness).....	PVC 0.61 mm
Core diameter.....	0.98 mm
Insulation resistance.....	Min 200M ohm x km
Conductor resistance.....	Max 31 Ω / KM
Maximum dielectric strength.....	1500 V / AC
Operating & storage temperature range.....	-20 to +70 °C
Rated voltage.....	48 V / DC
Rated current.....	6 A
Conductor structure.....	Twisted