

---

## FLRY-B Cable 0.5 mm<sup>2</sup>

Jacket, outer dimension:	PVC 1.6mm
No. of conductors:	16 x 0.21mm
Strand per conductor:	0.5 mm <sup>2</sup>
Color:	Grey
Packaging:	black spool
Length:	50 meter
Conductor material:	copper
Insulation material (with thickness):	PVC 0.37mm
Core diameter:	0.85mm
Insulation resistance:	Min 200M $\Omega$ x km
Maximum dielectric strength:	800V / AC
Temperature range:	-20 to +105 °C
Rated voltage:	12/24V
Rated current:	4A