

Data Sheet

LiY-Z wire 2 x 0.40 mm²



Rated Voltage: 48 V

Jacket, outer diameter: PVC 1.7 x 3.9 mm

Cross section area: 2 x 0.4 mm²

CCA strand per conductor: 12 x 0.2 mm

Color: Red/ Black

AWG: 21 AWG

Dielectric strength: 200M Ω KM

Max. current: 3.2 A

Operating temperature: -20°C to 70°C