

Item no.: 1567167 4 x 0.08 mm²
 1564535 6 x 0.08 mm²
 1564536 8 x 0.08 mm²
 1572268 10 x 0.08 mm²

Data Sheet

Flat Telephone Cable



Technical data

Rated voltage 48V
 Nominal current 1A
 Temperature range (min.) -20°C
 Temperature range (max.) 70°C
 Strand per conductor 7 x 0.12 mm
 Conductor material CCA
 Color Black
 AWG 28AWG
 Packaging 50 meter spool
 Capacitance 140pF

BN	Jacker, outer dimension	Cross section area
1567167	PVC 4.8 x 2.4 mm	4 x 0.08 mm ²
1564535	PVC 6.8 x 2.5 mm	6 x 0.08 mm ²
1564536	PVC 8.5 x 2.5 mm	8 x 0.08 mm ²
1572268	PVC 10.2 x 2.4 mm	10 x 0.08 mm ²