

## Data Sheet

---

### Jumper cable 2x 0.28 mm<sup>2</sup> red, white 20 m



#### Technical data

Jacket, outer dimension: PVC 1.0mm

Length: 20 meter

No. of conductors: 2 x 0.6 mm

Strand per conductor: 0.282 sqmm

Color: white/red

Material: CCA

Packaging: black spool

Material of Insulation: PVC

Conductor resistance (Ohm/km): Max 152.48 ohm/km(0.282sqmm)

Insulation resistance: Min 200M ohm x km

Rated voltage: 48V

Maximum of current: 0.6A

Operating temperature: -20 to +70 C

Type of flammability: IEC60332-1/EN50265-2-1