

Data Sheet

LiFY 1 x 0.75 mm² black 10 m



Technical data

nominal voltage	1000 V
Cable type	LiFY
Material (details)	copper
Outside Ø	2 mm
Number of wires	1 x
Strand construction	96 x 0.1 mm
Cross section (per wire)	0.75 mm ²
cross-section	1 x 0.75 mm ²
content	10 m
Temperature range, fixed installation (max.)	+90 ° C
Temperature range, fixed installation (min.)	-30 ° C
Manufacturer color	black