

Data Sheet

YV Jumper Wire 0.2 mm²

Jacket, outer dimension	PVC 1.1mm
No. of conductors	1 x 0.5mm
Strand per conductor	0.2 sqmm
Length	25 meter
Conductor material	Tinned - copper
Insulation material (with thickness)	PVC 0.3mm
Core diameter	0.5mm
Insulation resistance	Min 200M ohm x km
Conductor resistance	Max 110Ω/KM
Maximum dielectric strength	800V / AC
Temperature range	-20 to +70°C
Rated voltage	AC 50V / DC 75V
Rated current	1.6A
Conductor structure	One core