

Datasheet

Item no. 1568967 (Red)
1568968 (Black)
1568969 (Blue)

V1_1017_01_en

CCA Power Cable , 4.0 mm² , OD: 5.0 mm

Jacket, outer dimension.....	PVC 5.0 mm
Length.....	5 meter
No. of conductors.....	7 x 23 x 0.18 mm
Strand per conductor.....	4 mm ²
Conductor material	CCA
Insulation material	PVC
Dielectric strength	26 MV/m
Rated voltage.....	< AC 50V / DC 75V
Max. load capacity.....	10 A
Conductor resistance.....	10.1ohm/km
Insulator resistance.....	Min 200M ohm x km
Operating temperature.....	-20 to +70 C
Storage temperature range.....	-20 to +70 C
Operating humidity range.....	35%~95%
Storage humidity range.....	35%~95%

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

© Copyright 2017 by Conrad Electronic SE.