

Data Sheet

Heat shrinkable cable end caps with spiral adhesive coating – AEC series



Operating temperature range:

Continuous operation temperature: -55°C~110°C

Minimum shrink temperature: 80°C

Full recovery temperature: above 120°C

As supplied dia (pre-shrinkage) : 40mm

Fully recovered dia. (post-shrinkage): 15mm

Shrinking ratio: 2:1

Length: 83 mm