

Datasheet

Item no. 1570251 – 10 Meter, 1570929 – 25 Meter

V1_06132018_01_en

1567171 – 50 Meter, 1567172 – 100 Meter

Coaxial Cable RG6U

Construction:	Ø1.1 mm CCS + Ø5.0mm FOAM PE + 0.05 mm Double AL Foil + 7 x 16 x 0.12 mm Al-Mg Alloy Wire 75% Braiding + Ø6.8mm PVC sheath
Conductor OD:	1.1 mm CCS
Dielectric OD:	5.0 mm Foam Polythene
Sheath inside:	0.05 mm Thickness Double Aluminum Foil
Braiding:	7 x 16 x 0.12 Aluminum-Magnesium Alloy Wire Braiding
Sheath OD:	6.8 mm ROHS PVC
Rated Voltage:	48V/ DC
Electrical Properties:	Nominal Impedance: 75+/-3 Ω Nom. Capacitance: 53 pF/m Screening Factor: >85 db Nominal Velocity of Propogation: 82 %

Max. Att	MHz	5	55	211	450	600	750	778	865	1000	1350	2279.32
(dB/100m)	dB	10.6	15.04	18.41	22.83	25.86	28.68	29.29	30.87	33.44	39.4	52.83