Item No.: 1570252

Data Sheet

Alarm Cable 4 x 0.14 mm, 50 meters



Product Specification:

Jacket, outer dimension.....PVC 4mm
Cross section area.....4x0.14sqmm
CCA Strand per conductor.....7x0.16mm
Color..... white
AWG..... 26AWG
Dielectric strength..... .. 200M ohm KM
Capacitance..... 45PF
Material of the fine wire.....CCA
Conductor resistance.....250ohm/KM
Operation Voltage.....48V
Temperature range.....min. -20°C ,max. 70°C