

## Data Sheet

---

LiFY 1 x 1.5 mm<sup>2</sup> 10 m



## Technical data

nominal voltage	1000 V
Cable type	LiFY
Material (details)	copper
Outside Ø	2.7 mm
Number of wires	1 x
Strand construction	85 x 0.15 mm
Cross section (per wire)	1.5 mm <sup>2</sup>
cross-section	1 x 1.5 mm <sup>2</sup>
content	10 m
Temperature range, fixed installation (max.)	+70 ° C
Temperature range, fixed installation (min.)	-20 ° C
Manufacturer color	Black