

Panel mount XLR connector, male, 3 pin

No. 1570537



Color.....	Black
No. of pins.....	3
Audio Channel.....	Stereo
Contact plated.....	Nickel
Connection.....	Soldering
Category.....	Panel mount XLR male
Connector type.....	Plug, straight
Mating cycles.....	> 3000
Dimension.....	26.5*31.1*25.85 mm
Tolerance.....	±1 mm
Housing material & coating.....	Zinc alloy/black nickel plating
Contact resistance.....	≤ 6 m Ω
Mechanical life (cycles).....	>1000 cycles
Insertion and withdrawal force.....	≤ 20 N
Cable diameter can be used.....	N/A
Dielectric strength.....	1.2 kV dc
Operation voltage.....	50 V ac
Operation temperature and humidity.....	-25 degree Celsius to +80 degree Celsius / 10%-90%
Storage temperature and humidity.....	-25 degree Celsius to +80 degree Celsius / 10%-90%