Item No. 1570913


Data Sheet

BNC Plug Adapter









Specification

Frequency Range: DC-1GHz
Normal Impedance: 50Ω
Voltage Rating: 12VDC
Current Rating: 5A
Contact Resistance:
Center 1.5mΩ And Outer 0.2mΩ
Dielectric Withstanding Voltage: 1500V
Wire Range: 26-14AWG
Torque: 0.4Nm(3.51b/in)
Operating Temperature: -40℃ to 105℃
Strip Length: 6mm