



RJ45 Connector CAT5e

Support twisted pair size:	24 AWG
Voltage Rating:	30V
Frequency Range:	Wire 200 mating cycles ≥ 750
Fire Rating:	UL-94V-2
Color:	White
Module Weight:	6.2 g
Insulation Resistance:	Min. 500m Ω
Terminals:	8P8C
Operating Temperature:	10°C to 60°C
Storage Temperature:	40 °C to 70°C
Operating Humidity:	95% (non-condensing)