

Solder Splice Connector



b/n	Model	Max bundle dia.	Length	Color
1566693 1570915 (30pcs/ set)	JFST-1-W	1.7mm	25mm	White
1566694 1571404 (30pcs/ set)	JFST-2-R	2.7mm	40mm	Red
1565116 1570916 (30pcs/ set)	JFST-3-B	4.5mm	40mm	Blue
1566695 1571405 (30pcs/ set)	JFST-4-Y	6mm	40mm	Yellow

Shrinking ratio : 2:1

Adhesive lined waterproof for wiring splices

Operating Temperature-55°C ~ 105°C
 Fully recovery temperature at 110°C
 Tube Max. Heat Resistance 135°C
 Temperature of fully solder melt at 115°C
 Breakdown Voltage1kv
 Max. Current27A
 Max. Voltage600V