

Item no.: 1571458

Data Sheet

Flex LIY-Z Cable



Rated Voltage.....	48V
Temperature range.....min.	-20°C
Temperature range.....max.	70°C
Jacket, outer dimension.....	PVC 1.3 x 2.7mm
Cross section area.....	2 x 0.14 mm ²
CCA strand per conductor.....	7 x 0.16 mm
Color.....	Red/ Black
AWG.....	26 AWG
Packaging.....	20 meter per spool
Dielectric strength.....	2.5KV
Max current.....	1A
Halogen free.....	NO