

Data Sheet

12 feet Coil cord with banana plug & female snap (10 mm), blue



Technical data

Type: SpKL-10-366-SK

Cord type: Spiral cord

Insulation: PVC

Color: Blue

Cord length: 3.66 m

Contact: 10 mm press stud to Alligator Clip

Electrical resistance: 1 Mohm

Temperature range: -20 ~ 80 °C