


## **Datasheet**

Item no. 1567718

V1\_04092018\_01\_en

## **Ferrules with PVC insulation**

**Tined Copper** 



WIRE RANGE			Dimension					
mm²	AWG	Model	F	L	W	С	D	Color
mm-	AWG		±0.2	±1.0	±0.2	±0.1	±0.1	
0.14	26	E014-06GY	6.0	10.0	1.6	0.7	0.9	Grey
0.14	26	E014-06BN	6.0	10.0	1.6	0.7	0.9	Brown
0.25	24	E025-06VL	6.0	10.0	1.9	0.8	1.0	Violet
0.3	26-24	E030-06YL	6.0	10.5	2.5	0.8	1.1	Yellow
0.3	26-24	E030-06LB	6.0	10.5	2.5	0.8	1.1	Light Blue
0.34	24-22	E034-06CL	6.0	10.0	1.9	0.8	1.0	Crimson Lake
0.34	24-22	E034-06TB	6.0	10.0	1.9	8.0	1.0	Turquoise Blue
0.5	22-20	E050-08OR	8.0	14.0	2.6	1.0	1.3	Orange
0.5	22-20	E050-08WT	8.0	14.0	2.6	1.0	1.3	White
0.75	20-18	E075-08GY	8.0	14.6	2.8	1.2	1.5	Grey
0.75	20-18	E075-08LB	8.0	14.6	2.8	1.2	1.5	Light Blue
0.75	20-18	E075-08WT	8.0	14.6	2.8	1.2	1.5	White
1.0	18	E10-08YL	8.0	14.6	3.0	1.4	1.7	Yellow
1.5	16	E15-08RD	8.0	14.6	3.5	1.7	2.0	Red
1.5	16	E15-08BK	8.0	14.6	3.5	1.7	2.0	Black
2.5	14	E 25-08BL	8.0	15.2	4.0	2.3	2.6	Blue
2.5	14	E25-08GY	8.0	15.2	4.0	2.3	2.6	Grey
4	12	E40-09GY	9.0	16.5	4.4	2.8	3.2	Grey
4	12	E40-09OR	9.0	16.5	4.4	2.8	3.2	Orange
6	10	E60-12YL	12.0	20.0	6.3	3.5	3.9	Yellow
6	10	E60-12GN	12.0	20.0	6.3	3.5	3.9	Green
6	10	E60-12RD	12.0	20.0	6.3	3.5	3.9	Red
6	10	E60-12BK	12.0	20.0	6.3	3.5	3.9	Black
10	8	E100-18IW	18.0	27.5	7.6	4.5	4.9	lvory
10	8	E100-18RD	18.0	27.5	7.6	4.5	4.9	Red
10	8	E100-12BN	12.0	21.5	7.6	4.5	4.9	Brown
16	6	E160-12BL	12.0	22.2	8.8	5.8	6.2	Blue
16	6	E160-12IW	12.0	22.2	8.8	5.8	6.2	Ivory
16	6	E160-12GN	12.0	22.2	8.8	5.8	6.2	Green

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.