
Item No. 1572430


Data Sheet


Crimp Cable Ferrules, Twincable Ferrules With PVC Insulation 2x0.75mm², Grey, 100pcs











Specification

Material : Terminal - Tined Copper
Insulation - PVC
Max. temp. resistance - 75℃
Wire Range: 2 × 0.75mm2
Type Of Connector: AWG 2 × 20