



Technical requirement:

1. The product should be followed with Cat 6A connection and technical standard;
2. Unmarked tolerance dimension on the basis of SJ/T10628 - 1995 6 grade;
3. ROHS2.0 ADN REACH COMPLIANT
4. Operation temperature: -10°C ~ +60°C
Storage temperature: -40°C ~ +70°C
Operation humidity: 30%~80%
Storage humidity: 30%~80%
5. PACKING: 1PCS/Renkforce color box (SIZE: 105 x 20 x 140mm)

MATERIAL LIST:

⑥	Contact	8P8C 3U" Gold Plated	8	
⑤	Base	ABS	1	
④	roof cover	ABS	1	
③	shielded enclosure	Nickel Plated brass t=0.3mm	2	
②	PCB	FR-4, t=0.8	1	
①	PCB outlet	PBT	2	
NO	MAT. NAME	DESCRIPTION	QT' Y	REMARK

Connection Method

- ① ————— ①
- ② ————— ②
- ③ ————— ③
- ④ ————— ④
- ⑤ ————— ⑤
- ⑥ ————— ⑥
- ⑦ ————— ⑦
- ⑧ ————— ⑧
- SHELL ————— SHELL

		NEW		2017.06.08		CUSTOMER		ITEM NO.	29212c121	
						PRODUCT NAME	CAT.6A STP Inline Coupler	UNO ITEM NO.	277202	UNIT MM
BY	CHK	REVISION RECORD MODIFICATIONS		DATE	REV.	DRAWNBY	CHECKBY	APPOBY	DATE	
						Alvan	Alvan		2017.06.08	