

Product Data Sheet Model No.: 079163-LA

Order code	EAN	Packaging - SKU
079163-LAB1	4895149079163	Color Gif Box, 1 pc/SKU
		70.0
	OP .	70.0
Product Category		LED cordless light
Series		SafeGuard RF1.1
Description		LED outdoor automotive motion sensor security light, one headlamp
Flastoiaal abausata	wiation.	
Electrical character Input Voltage	ristics	4.5VDC (3 x 1.5V AA batteries)
Operating Voltage		4.5V
Standby Current		<100µA
•		350mA
Lamp current Battery Life Time		600 days* (Based on 5 operation per day in Auto Mode)
Lighting characteri CCT uminous flux / Intensity		4500K-5500K ≥ 60 lm
LED Type	y	1 x SMD LED
Light modes		OFF / ON / AUTO
Light modes Light duration in auto n	nodo	10 s ±3 s
Light duration in auto n	node	10 \$ £3 \$
Sensors characteri	istics	
Sensor		Photo sensors & PIR Sensors
Sensor Detection Rang	ge	8M, 110°
Lux Detection Frequen	ncy	3 sec per detecion, 1 sec between detection
Trigger Lux Value		0-35 Lux
Physical Character		
Operating Temperature	е	-20°C to 50°C
Storage Temperature		-20°C to 50°C
Dimension		70.0 (L) x 159.3 (H) x 113.4 (D) mm
Weight		
Housing Material		PC
P Rating		IP55
		los pue
Product Compliance		CE, RoHS
Warranty		12 months from ex-factory date
* Based on new alkali	ine batteries. Do not mix n	ew and old batteries at the same time.

www.gp-lighting.com