
Product Feature

- LCD display : 2.0" TFT
- Resolution ratio : 320*240 LCD
- Audio format : MP3, WMA WAV, FLAC, APE, ACC, OGG,DSD (WMA can show in manual and packing)
- Top Class DAC chip
- Professional amplifier chip
- Micro SD memory card slots support up to 64GB card (no SD card included) (No Built-in memory, memory is only running internal program)
- CNC casing
- 2" QVGA display
- Standard 3.5mm headphone jack with 100 steps volume control
- Support 24 Bit 192KHz file
- English Lyrics only

Technical data

- WAV maximum support 24BIT 192KHz, APE/ FLAC maximum support 24BIT 192KHz
- SNR : ≥ 99 dB
- Large size built-in battery (1500mAh) ~ 25 hour's playback
- USB charging time : 5 hours with 500mA (with 5V, 1A Charger)
- Line output volume sync, -6dB or 0dB
- Playback : about 25hours (volume 30, for HIFI music) 30hours (for 320Kbps music)
- Volume control : 100 level, volume control
- Headphone output power : ≥ 80 mW
- Headphone output : stereo output
- Transmission interface : Micro 5 pin USB 2.0
- Max. current : 5V 500mA
- Max. file name length : 16 character
- LED indicator
 - Red : charging
 - Green : full charged

Standard data

- Dimensions : 88 x 56 x 16 mm (L x W x H)
- Weight: 0.109 kg (unit including battery) +/-5g
- Working temperature & humidity: -5°C ~ 40°C & 30 to 85 %
- Storage temperature and humidity : -5°C ~ 40°C & 30 to 85 %

Operating system support:

Windows Vista (32 & 64 bit)
Windows 7 (32 & 64 bit)
Windows 8.0 (32 & 64 bit)
Windows 8.1(32 & 64 bit)
Windows 10 (32 & 64 bit)
Windows 10S
Windows RT