



Product Name	DC5V 60LEDs/m 60pixels/m SK6812 SK6818 RGBW LED pixel strip
Item No.	
Power Consumption	24W/Meter
Work Voltage	DC5V
IC Type	sk6818/sk6812
LED Qty per meter	60pcs SMD5050RGBW, 60pixels/m
PCB Color	Black/white/yellow
Dimension	ca. L 5000*W10*H3mm
Waterproof Grade	IP40/IP65/IP67/IP68
Work Temperature	-30-+60°C
Life-span	50,000H
Certificate	CE&RoHS

DC5V 60LEDs/m 60pixels/m SK6818 SK6812 RGBW pixel LED strip light Advantage:

1. 4 different chips, red, green, blue and white in one 5050 LED package, IC embeded, new design
2. Not only 4 chips, IC also embeded, one LED one pixel
3. LED can show any color
4. Addressable, each pixel show customized color

DC5V 30LEDs/m 30pixels/m SK6818 SK6812 RGBW pixel LED strip light Connection:

DC+: connect to power supply DC+

DAT: connect to controller DAT

GND: connect to power supply GND & controller GND