

# Datasheet

Item no. 1576728, 1576729, 1576730



**Aufbau:**  
Keramikrohr  
**Kontaktkappen:**  
Messing, vernickelt

**Construction:**  
Ceramic tube  
**Contact caps:**  
Brass, nickel plated

## Bemessungswerte / Ratings

Art.-No.	Strom Current (A)	Spannung Voltage	Ausschaltvermögen Breaking capacity	Spannungsfall Voltage drop (Volt) max.	Max. Verlustleistung Max. Power dissip. [W]	Schmelzintegral Melting integral [A <sup>2</sup> s]
TC-UL632.727	10 A	250 V	750 A	0,139	2,26	817
TC-UL632.728	12 A	250 V	750 A	0,129	2,56	1277
TC-UL632.729	15 A	250 V	750 A	0,120	2,96	2123

Electrical Characteristics

Prüfstrom Testing current	Schmelzzeit / Blow Time	
	Minimum	Maximum
100 %	4 Hrs	N / A
135 %	N / A	1 Hr
200 %	5 sec	30 sec