

Datasheet

Item no. **1576906, 1576897, 1576907, 1576908, 1576909, 1576910, 1576911, 1576898, 1576892, 1576912, 1576914, 1576913**



Bemessungswerte / Ratings

Art.-No.	Strom Current	Voltage	Ausschaltvermögen Breaking capacity	Max . Leistungsverlust Power dissipation [W]
TC-1038314	0,5 A	500 V	120 kA	0,49
TC-1038317	1 A	500 V	120 kA	0,10
TC-1038320	2 A	500 V	120 kA	0,18
TC-1038323	4 A	500 V	120 kA	0,31
TC-1038325	6 A	500 V	120 kA	0,32
TC-1038326	8 A	500 V	120 kA	0,52
TC-1038327	10 A	500 V	120 kA	0,55
TC-1038328	12A	500 V	120 kA	0,63
TC-1038330	16 A	500 V	120 kA	0,92
TC-1038331	20 A	400 V	120 kA	0,96
TC-1038332	25 A	400 V	120 kA	1,40
TC-1038334	32 A	400 V	120 kA	1,80

Technische Änderungen sind vorbehalten! / Technical data subject to change! 08 / 2017