To. :

DATE : 20 . . .

RoHS	Halogen Free

SPECIFICATION

PRODUCT : STARCAP

MODEL : DCST series

WRITTEN	CHECKED	APPROVED

amec
Langer Acker 32
30900 Wedemark
Germany
(+49) 5130 / 58642-0
info@amec-gmbh.de
www.amec-gmbh.de

KORCHIP CORP.

KORCHIP B/D, 359, Manan-ro, Manan-gu, Anyang-si, Gyeonggi-do, KOREA

TEL : 82 - 31 - 361 - 8000

FAX : 82 - 31 - 361 - 8080

Index

Page No.	ITEM	etc.
1	Cover Page	
2	Index	
3	Revision History	
	Manufacturer Information	
4	1. Scope	
	2. Part Number System	
	3. Photo	
	4. General Specifications	
5-7	5. Product Construction and Dimension	
8	6. Reliability Specifications	
9	7. Packing Specifications	
10	8. Labeling Standards	
11	9. Measuring Method of Characteristics	
12	10. Mounting	
13-14	11. Cautions for Use	
15	12. Environmental Management	

amec
Langer Acker 32
30900 Wedemark
Germany
(+49) 5130 / 58642-0
info@amec-gmbh.de
www.amec-gmbh.de

Revision History

No.	Documentation	Check	Description of Revision	Approval	Date
1	S.E. Kim (R&D)	K.B. Chung (Q.A.)	Initial Release	B.I. Lim (R&D)	Apr. 24, 2015

amec
Langer Acker 32 (+49) 5130 / 58642-0
30900 Wedemark info@amec-gmbh.de
Germany www.amec-gmbh.de

Manufacturer Information

Manufacturer : Korchip Corporation

Location : KORCHIP B/D, 359, Manan-ro, Manan-gu, Anyang-si, Gyeonggi-do, KOREA

Tel. : +82-31-361-8000

Fax. : +82-31-361-8080

1. Scope

This specification applies to STARCAP(Electric Double Layer Capacitor), submitted to specified customer in cover page.

2. Part Number System

DCST	5R5	224	C	*(Example)*
①	②	③	④	

① Series Name : DC(**D**ouble layer capacitor - **C**oin type), S(**S**mall size), T(high **T**emp.)
② Rated Voltage : 5.5VDC
③ Capacitance : 0.22 F (224 = 22 × 10^{+4} uF)
④ Terminal Type : C-type

3. Photo

amec
Langer Acker 32
30900 Wedemark
Germany
(+49) 5130 / 58642-0
info@amec-gmbh.de
www.amec-gmbh.de

4. General Specifications

ITEMS	DCST5R5104C	DCST5R5224C	DCST5R5334C
Rated Voltage	5.5 VDC	5.5 VDC	5.5 VDC
Operating Temp.	-25 ~ +85 ℃	-25 ~ +85 ℃	-25 ~ +85 ℃
Capacitance	0.10 F	0.22 F	0.33 F
Capacitance Tolerance	-20 ~ 80 %	-20 ~ 80 %	-20 ~ 80 %
Equivalent Series Resistance (ESR)	Less than 120Ω	Less than 75Ω	Less than 75Ω
Leakage Current (LC, 30min.)	Less than 200㎂	Less than 330㎂	Less than 500㎂

5. Product Construction and Dimension



amec
Langer Acker 32
30900 Wedemark
Germany
(+49) 5130 / 58642-0
info@amec-gmbh.de
www.amec-gmbh.de

Part No.	Dimensions (mm)		
	ØD	H	P
DCST5R5104C	13.5	9.5	5.0
DCST5R5224C	13.5	9.5	5.0
DCST5R5334C	13.5	9.5	5.0

6. Reliability Specifications

<table>
<tr><th colspan="3">Item</th><th colspan="2">Specification</th><th colspan="2">Test Condition (JISC5102)</th></tr>
<tr><td rowspan="9">Temperature Characteristics</td><td>Capacitance Change</td><td rowspan="2">Step 2</td><td>Within ± 30% of Initial Value</td><td colspan="2" rowspan="9">Measure electrical characteristics after exposing STARCAP Capacitor to each temperature atmosphere for one(1) hour
<table><tr><th>Step</th><th>Temperature</th></tr><tr><td>1</td><td>20±2℃</td></tr><tr><td>2</td><td>-25±2℃</td></tr><tr><td>3</td><td>20±2℃</td></tr><tr><td>4</td><td>85±2℃</td></tr><tr><td>5</td><td>20±2℃</td></tr></table></td></tr>
<tr><td>ESR</td><td>5Times or less than Initial Value</td></tr>
<tr><td>Capacitance Change</td><td rowspan="3">Step 4</td><td>Within ± 30% of Initial Value</td></tr>
<tr><td>ESR</td><td>4Times or less than Initial Value</td></tr>
<tr><td>LC(30min.)</td><td>4Times or less than Initial Value</td></tr>
<tr><td>Capacitance Change</td><td rowspan="3">Step 5</td><td>Within ± 10% of Initial Value</td></tr>
<tr><td>ESR Change</td><td>Within ± 10% of Initial Value</td></tr>
<tr><td>LC Change (30min.)</td><td>Within ± 10% of Initial Value</td></tr>
<tr><td rowspan="4">Humidity Resistance</td><td colspan="2">Capacitance Change</td><td>± 30% of Initial Value</td><td colspan="2" rowspan="4">Temp. : 40±2℃
Humidity : 90 ~ 95%RH
Time : 240±8 Hours
<u>No Voltage Applied</u></td></tr>
<tr><td colspan="2">ESR</td><td>3Times or less than Spec. Value</td></tr>
<tr><td colspan="2">LC(30min.)</td><td>2Times or less than Spec. Value</td></tr>
<tr><td colspan="2">Appearance</td><td>No Marked Defect</td></tr>
<tr><td rowspan="2">Self Discharge Characteristics</td><td colspan="2" rowspan="2">Voltage</td><td rowspan="2">More than 4.2Vdc</td><td>Charging Condition</td><td>Voltage : 5.5Vdc
Current : 50㎃
Charge Time : 24 Hours</td></tr>
<tr><td>Self Discharge Condition</td><td>Duration : 24 Hours
Temp. : Less than 25℃
Humidity : Less than 70%RH</td></tr>
<tr><td rowspan="4">Vibration Resistance</td><td colspan="2">Capacitance</td><td>Spec. Value</td><td colspan="2" rowspan="4">Amplitude : 1.5㎜
Frequency : 10 ~ 55㎐
Direction : X, Y, Z 3 Directions
Test Time : 6 Hours</td></tr>
<tr><td colspan="2">ESR</td><td>Spec. Value</td></tr>
<tr><td colspan="2">LC(30min.)</td><td>Spec. Value</td></tr>
<tr><td colspan="2">Appearance</td><td>No Marked Defect</td></tr>
<tr><td>Terminal Strength</td><td colspan="2" rowspan="2">Appearance</td><td rowspan="2">Terminals shall not be separated</td><td colspan="2">Load 1kg , 10±1 Sec.</td></tr>
<tr><td>Terminal Bend Strength</td><td colspan="2">Load 1kg , Angle 90º , 1Cycle</td></tr>
<tr><td rowspan="4">Endurance</td><td colspan="2">Capacitance Change</td><td>Within ± 30% of Initial Value</td><td colspan="2" rowspan="4">Temp. : 85±2℃
Test Time : 1,000(+24,-0) Hours
Applied Voltage : 5.5Vdc</td></tr>
<tr><td colspan="2">ESR</td><td>4Times or less than Initial Value</td></tr>
<tr><td colspan="2">LC(30min.)</td><td>Spec. Value</td></tr>
<tr><td colspan="2">Appearance</td><td>No Marked Defect</td></tr>
<tr><td rowspan="4">Cycle Characteristics</td><td colspan="2">Capacitance Change</td><td>Within ± 30% of Initial Value</td><td colspan="2" rowspan="4">Temp. : 25±2℃
Cycle No. : 10,000
Charge Voltage : 5.5Vdc
Resistance : 100Ω, Time : 9min.
Discharge Resistance:100Ω, Time:1min.</td></tr>
<tr><td colspan="2">ESR</td><td>4Times or less than Initial Value</td></tr>
<tr><td colspan="2">LC(30min.)</td><td>Spec. Value</td></tr>
<tr><td colspan="2">Appearance</td><td>No Marked Defect</td></tr>
</table>

amec Langer Acker 32 30900 Wedemark Germany (+49) 5130/ 3884-90 info@amec-gmbh.de www.amec-gmbh.de

7. Packing Specifications

Part No.	Quantity (PCS)			Size (W × L × H mm)		Type
	Vinyl Bag	Inner Box	Outer Box	Inner Box	Outer Box	
DCST5R5104C	500	1,000	2,000	240×220×100	460×260×125	Bulk
DCST5R5224C	500	1,000	2,000	240×220×100	460×260×125	Bulk
DCST5R5334C	500	1,000	2,000	240×220×100	460×260×125	Bulk

8. Labeling Standards



amec
Langer Acker 32
30900 Wedemark
Germany
info@amec-gmbh.de
www.amec-gmbh.de

Lot No. System

Ex.) S X B A C 002

① ② ③ ④ ⑤ ⑥

① Product Code : S (STARCAP)

② Production Year Code : X (2013), Y (2014), Z (2015)…

③ Factory Identification Code : B (Factory 2)

④ Production Month Code : A (Jan.), B (Feb.), … , J (Oct.), K (Nov.), L (Dec.)

⑤ Production Date Code : 1 (1st), 2 (2nd), … , 9 (9th), A (10th), B (11th), C (12th) … Q (26th), R (27th), S (28th), … , V (31th)

⑥ Lot Issuing Serial Code : 001 (First lot of a specific day), 002 (Second lot of a specific day), 003 (Third lot of a specific day)…

9. Measuring Method Of Characteristics

Capacitance	1) Charge the STARCAP with constant current 50±0.1㎃ to the voltage of V1(=4.4V) for 30 min. 2) Discharge the STARCAP with constant current(A) 2±0.1㎃ to the voltage of V2(=2.2V) while measure the discharge time(T). 3) Calculate capacitance using the following formula.  C = A(Ampere) × T sec / (V_1-V_2)V [F] 
Equivalent Series Resistance (ESR @1kHz)	● Measure ESR by the LCR meter. (Frequency:1㎑, Bias Voltage : $0^{+0.05}$V) or ● Calculate ESR using the following formula.  ESR[Ω] = V / i **R[Ω] = V[V] / I[A]** * i[㎃] = I[A] x 10^{-3} R : Internal resistance(ESR) [Ω] V : Measured voltage between terminals [V] i : Current 1mA(A.C.)
Leakage Current	1) Apply 5.0±0.1V to the STARCAP.(E_0) 2) Measure V_R after 30±0.5 min. 3) Calculate current using the following formula.  *LC = (V_R/R_C) x 10^3 [mA]* V_R = Measured value R_C = 100Ω (0.1F ~ 0.33F)
☞ The STARCAP should be shorted before each measurement as follows ; Capacitance : 60 min. , ESR : 15 min. , LC : 15 min.	

amec
Langer Acker 32 (+49) 5130 / 38642-0
30900 Wedemark info@amec-gmbh.de
Germany www.amec-gmbh.de

10. Mounting

When you solder STARCAP to a printed circuit board, excessive thermal stress could cause the STARCAP's electrical characteristics to deteriorate, compromise the integrity of the seal or cause the electrolyte to leak due to increased internal pressure.

① Recommended condition of flow soldering



Pre-heating Temp.	: Max. 100 ℃ (on the surface of STARCAP)
Pre-heating Time	: Max. 60seconds
PCB Thickness	: Min. 0.8mm

amec
Kanalstrasse 32
30900 Wedemark
Germany
(+49) 5130 / 58642-0
info@amec-gmbh.de
www.amec-gmbh.de

② Recommended condition of manual soldering

- Soldering Tip Temp. : 350℃ or less
- Soldering Time : 3 sec. or less
- Times : Three times or less at intervals of 9 sec. or more

※ Do not touch the metal case of STARCAP with a soldering iron.

③ It is not allowed to go through reflow (IR, Atmosphere heating methods etc.) process.

④ The terminals are plated for good solderability. Rasping terminals may damage the plating layer and degrade the solderability.

Do not apply a large force to the terminals. Otherwise, they may break or come off or the STARCAP characteristics may be deteriorated.

11. Cautions for Use

Please be careful for following points when you use STARCAP.

1) Do not apply more than rated voltage.

If you apply more than rated voltage, STARCAP's electrolyte will be decomposed and its ESR increase. At the worst, it may be broken.

2) Do not use STARCAP for ripple absorption.

3) Polarity

Please mount it in accordance with its polarity.

4) Operating temperature and life

Generally, STARCAP has a lower leakage current, longer back-up time and longer life in the low temperature i.e. the room temperature. But it has a higher leakage current, shorter back-up time and shorter life in the high temperature.

Please design to keep STARCAP away from calorific parts.

amec
Kaiserin-Augusta-Allee 33 (+49) 5130 / 58642-0
30900 Wedemark info@amec-gmbh.de
Germany www.amec-gmbh.de

5) Cleaning

Some detergent or high temperature drying causes deterioration of STARCAP.
If you wash STARCAP, Consult us.

6) Following figure shows the general back-up circuit.



D : Diode to prevent the reverse current
R : Resistor to control the charging current

7) Short-circuit STARCAP

DO NOT short-circuit between terminals of STARCAP without resistor.

8) Storage

In long term storage, please store STARCAP in following condition;

① TEMP. : 15 ~ 35 ℃

② HUMIDITY : 45 ~ 75 %RH

③ Non-dust, non-acidic and/or non-alkaline atmosphere

④ Avoid direct sun light, strong magnetic field

Storage period limit is one(1) year when a STARCAP is stored in the above condition. Storage in improper condition may cause some damage on terminal surface or on outer tube of STARCAP.

9) Do not disassemble STARCAP. It contains electrolyte.

10) Series connection of STARCAP

Over-rated voltage may be applied to a single STARCAP in series connection due to the deviation of capacitance and ESR of each STARCAP. Please inform us if you are using STARCAP in series connection and please design so as not to apply over-rated voltage to each STARCAP, and use STARCAPs from same lot.

amec
Ernst-Abbe-Str. 32
30900 Wedemark
Germany
(+49) 5130 / 58642-0
info@amec-gmbh.de
www.amec-gmbh.de

11) The tips of STARCAP terminals are very sharp. Please handle with care.

12. Environmental Management

All STARCAP products are RoHS compliant, Halogen Free and environment friendly.

Series	RoHS directive (Pb, Cr+6, Hg, Cd, PBB,PBDE)	ELV directive (Pb, Cr+6, Hg, Cd)	PVC	Halogen Flame Retardant Free (Cl, Br)	etc.
DCST	N.D.	N.D.	N.D.	N.D.	

* N.D. : Not detected

amec
Langer Acker 32
30900 Wedemark
Germany
(+49) 5130 / 58642-0
info@amec-gmbh.de
www.amec-gmbh.de