

# Datasheet

Material: Nylon 66, 94V-2 certificated by UL-Heat-resisting, acid & erosion-control, insulate well and not apt to age.  
 Operating temperature: -35 °C to 85 °C



Item No	Product Description	Bundle Diameter(mm)	Tensile Strength	
			LBS	KGS
1577914	cable tie, 1.9*60mm Black	2-11	14	6.5
1577915	cable tie, 1.9*60mm White	2-11	14	6.5
1577916	cable tie, 1.9*80mm Black	2-18	14	6.5
1577917	cable tie, 1.9*80mm White	2-18	14	6.5
1577918	cable tie, 1.9*100mm Black	2-22	14	6.5
1577919	cable tie, 1.9*100mm White	2-22	14	6.5
1577920	cable tie, 1.9*120mm Black	2-30	14	6.5
1577921	cable tie, 1.9*120mm White	2-30	14	6.5
1577922	cable tie, 1.9*150mm Black	2-35	14	6.5
1577923	cable tie, 1.9*150mm White	2-35	14	6.5
1577924	cable tie, 1.9*200mm Black	2-50	14	6.5
1577925	cable tie, 1.9*200mm White	2-50	14	6.5
1577926	cable tie, 2.0*80mm Black	2-18	14	6.5
1577927	cable tie, 2.0*80mm White	2-18	14	6.5
1577928	cable tie, 2.0*100mm Black	2-22	14	6.5
1577929	cable tie, 2.0*100mm White	2-22	14	6.5
1577930	cable tie, 2.0*120mm Black	2-30	14	6.5
1577931	cable tie, 2.0*120mm White	2-30	14	6.5
1577932	cable tie, 2.2*120mm Black	2-30	18	8
1577933	cable tie, 2.2*120mm White	2-30	18	8
1577934	cable tie, 2.2*150mm Black	2-35	18	8
1577935	cable tie, 2.2*150mm White	2-35	18	8
1577936	cable tie, 2.2*200mm Black	3-50	18	8
1577937	cable tie, 2.2*200mm White	3-50	18	8

Item No	Product Description	Bundle Diameter(mm)	Tensile Strength	
			LBS	KGS
1577938	cable tie, 2.3*180mm Black	2-42	18	8
1577939	cable tie, 2.3*180mm White	2-42	18	8
1577940	cable tie, 2.5*80mm Black	2-16	18	8
1577941	cable tie, 2.5*80mm White	2-16	18	8
1577942	cable tie, 2.5*100mm Black	2-22	18	8
1577943	cable tie, 2.5*100mm White	2-22	18	8
1577944	cable tie, 2.5*120mm Black	2-30	18	8
1577945	cable tie, 2.5*120mm White	2-30	18	8
1577946	cable tie, 2.5*150mm Black	2-35	18	8
1577947	cable tie, 2.5*150mm White	2-35	18	8
1577948	cable tie, 2.5*200mm Black	3-50	18	8
1577949	cable tie, 2.5*200mm White	3-50	18	8
1577950	cable tie, 2.6*150mm Black	2-35	18	8
1577951	cable tie, 2.6*150mm White	2-35	18	8
1577952	cable tie, 2.6*200mm Black	3-50	18	8
1577953	cable tie, 2.6*200mm White	3-50	18	8
1577954	cable tie, 2.8*180mm Black	3-42	27	12
1577955	cable tie, 2.8*180mm White	3-42	27	12
1577956	cable tie, 2.8*200mm Black	3-50	27	12
1577957	cable tie, 2.8*200mm White	3-50	27	12
1577958	cable tie, 2.8*250mm Black	3-65	27	12
1577959	cable tie, 2.8*250mm White	3-65	27	12
1577960	cable tie, 2.8*300mm Black	3-80	27	12
1577961	cable tie, 2.8*300mm White	3-80	27	12
1577962	cable tie, 3.0*150mm Black	3-35	33	15
1577963	cable tie, 3.0*150mm White	3-35	33	15
1577964	cable tie, 3.0*250mm Black	3-65	33	15
1577965	cable tie, 3.0*250mm White	3-65	33	15
1577966	cable tie, 3.2*200mm Black	3-50	40	18
1577967	cable tie, 3.2*200mm White	3-50	40	18
1577968	cable tie, 3.2*250mm Black	3-65	40	18
1577969	cable tie, 3.2*250mm White	3-65	40	18
1577970	cable tie, 3.2*300mm Black	3-80	40	18
1577971	cable tie, 3.2*300mm White	3-80	40	18
1577972	cable tie, 3.3*120mm Black	3-30	40	18
1577973	cable tie, 3.3*120mm White	3-30	40	18
1577974	cable tie, 3.3*180mm Black	3-42	40	18
1577975	cable tie, 3.3*180mm White	3-42	40	18
1577976	cable tie, 3.6*140mm Black	3-33	40	18
1577977	cable tie, 3.6*140mm White	3-33	40	18
1577978	cable tie, 3.6*150mm Black	3-35	40	18
1577979	cable tie, 3.6*150mm White	3-35	40	18
1577980	cable tie, 3.5*250mm Black	3-65	40	18
1577981	cable tie, 3.5*250mm White	3-65	40	18
1577982	cable tie, 3.5*300mm Black	3-80	40	18
1577983	cable tie, 3.5*300mm White	3-80	40	18
1577984	cable tie, 3.6*200mm Black	3-50	40	18

Item No	Product Description	Bundle Diameter(mm)	Tensile Strength	
			LBS	KGS
1577985	cable tie, 3.6*200mm White	3-50	40	18
1577986	cable tie, 3.6*250mm Black	3-65	40	18
1577987	cable tie, 3.6*250mm White	3-65	40	18
1577988	cable tie, 3.6*300mm Black	3-80	40	18
1577989	cable tie, 3.6*300mm White	3-80	40	18
1577990	cable tie, 3.6*350mm Black	3-90	40	18
1577991	cable tie, 3.6*350mm White	3-90	40	18
1577992	cable tie, 3.6*370mm Black	3-98	40	18
1577993	cable tie, 3.6*370mm White	3-98	40	18
1577994	cable tie, 3.6*400mm Black	3-105	40	18
1577995	cable tie, 3.6*400mm White	3-105	40	18
1577996	cable tie, 3.6*450mm Black	3-130	40	18
1577997	cable tie, 3.6*450mm White	3-130	40	18
1577998	cable tie, 3.6*500mm Black	3-150	40	18
1577999	cable tie, 3.6*500mm White	3-150	40	18
1578000	cable tie, 3.8*200mm Black	3-50	40	18
1578001	cable tie, 3.8*200mm White	3-50	40	18
1578002	cable tie, 4.0*250mm Black	3-65	40	18
1578003	cable tie, 4.0*250mm White	3-65	40	18
1578004	cable tie, 4.0*300mm Black	3-80	40	18
1578005	cable tie, 4.0*300mm White	3-80	40	18
1578006	cable tie, 4.6*350mm Black	3-90	50	22
1578007	cable tie, 4.6*350mm White	3-90	50	22
1578008	cable tie, 4.6*380mm Black	3-102	50	22
1578009	cable tie, 4.6*380mm White	3-102	50	22
1578010	cable tie, 4.6*400mm Black	3-105	50	22
1578011	cable tie, 4.6*400mm White	3-105	50	22
1578012	cable tie, 4.6*500mm Black	3-150	50	22
1578013	cable tie, 4.6*500mm White	3-150	50	22
1578014	cable tie, 4.8*200mm Black	3-50	50	22
1578015	cable tie, 4.8*200mm White	3-50	50	22
1578016	cable tie, 4.8*200mm Black (thick 1.4 mm)	3-50	50	22
1578017	cable tie, 4.8*200mm White (thick 1.4 mm)	3-50	50	22
1578018	cable tie, 4.8*250mm Black	3-65	50	22
1578019	cable tie, 4.8*250mm White	3-65	50	22
1578020	cable tie, 4.8*300mm Black	3-80	50	22
1578021	cable tie, 4.8*300mm White	3-80	50	22
1578022	cable tie, 4.8*350mm Black	3-90	50	22
1578023	cable tie, 4.8*350mm White	3-90	50	22
1578024	cable tie, 4.8*370mm Black	3-98	50	22
1578025	cable tie, 4.8*370mm White	3-98	50	22
1578026	cable tie, 4.8*400mm Black	3-105	50	22
1578027	cable tie, 4.8*400mm White	3-105	50	22
1578028	cable tie, 4.8*450mm Black	3-130	50	22
1578029	cable tie, 4.8*450mm White	3-130	50	22
1578030	cable tie, 4.8*500mm Black	3-150	50	22

Item No	Product Description	Bundle Diameter(mm)	Tensile Strength	
			LBS	KGS
1578031	cable tie, 4.8*500mm White	3-150	50	22
1578032	cable tie, 5.2*200mm Black	3-50	65	30
1578033	cable tie, 5.2*200mm White	3-50	65	30
1578034	cable tie, 5.2*250mm Black	3-65	65	30
1578035	cable tie, 5.2*250mm White	3-65	65	30
1578036	cable tie, 5.2*300mm Black	3-80	65	30
1578037	cable tie, 5.2*300mm White	3-80	65	30
1578038	cable tie, 5.2*350mm Black	3-90	65	30
1578039	cable tie, 5.2*350mm White	3-90	65	30
1578040	cable tie, 5.2*400mm Black	3-105	65	30
1578041	cable tie, 5.2*400mm White	3-105	65	30
1578042	cable tie, 5.5*450mm Black	3-130	65	30
1578043	cable tie, 5.5*450mm White	3-130	65	30
1578044	cable tie, 5.5*500mm Black	3-150	65	30
1578045	cable tie, 5.5*500mm White	3-150	65	30
1578046	cable tie, 5.8*200mm Black	3-50	65	30
1578047	cable tie, 5.8*200mm White	3-50	65	30
1578048	cable tie, 5.8*250mm Black	3-65	65	30
1578049	cable tie, 5.8*250mm White	3-65	65	30
1578050	cable tie, 5.8*300mm Black	3-80	65	30
1578051	cable tie, 5.8*300mm White	3-80	65	30
1578052	cable tie, 5.8*350mm Black	3-90	65	30
1578053	cable tie, 5.8*350mm White	3-90	65	30
1578054	cable tie, 5.8*400mm Black	3-105	65	30
1578055	cable tie, 5.8*400mm White	3-105	65	30
1578056	cable tie, 6.0*200mm Black	3-50	65	30
1578057	cable tie, 6.0*200mm White	3-50	65	30
1578058	cable tie, 7.2*200mm Black	3-50	120	55
1578059	cable tie, 7.2*200mm White	3-50	120	55
1578060	cable tie, 7.2*250mm Black	4-65	120	55
1578061	cable tie, 7.2*250mm White	4-65	120	55
1578062	cable tie, 7.2*300mm Black	4-80	120	55
1578063	cable tie, 7.2*300mm White	4-80	120	55
1578064	cable tie, 7.2*350mm Black	4-90	120	55
1578065	cable tie, 7.2*350mm White	4-90	120	55
1578066	cable tie, 7.2*400mm Black	4-405	120	55
1578067	cable tie, 7.2*400mm White	4-105	120	55
1578068	cable tie, 7.2*450mm Black	4-110	120	55
1578069	cable tie, 7.2*450mm White	4-110	120	55
1578070	cable tie, 7.2*500mm Black	4-150	120	55
1578071	cable tie, 7.2*500mm White	4-150	120	55
1578072	cable tie, 7.2*650mm Black	4-190	120	55
1578073	cable tie, 7.2*650mm White	4-190	120	55
1578074	cable tie, 7.6*200mm Black	4-50	120	55
1578075	cable tie, 7.6*200mm White	4-50	120	55
1578076	cable tie, 7.6*250mm Black	4-65	120	55
1578077	cable tie, 7.6*250mm White	4-65	120	55

Item No	Product Description	Bundle Diameter(mm)	Tensile Strength	
			LBS	KGS
1578078	cable tie, 7.5*300mm Black	4-80	120	55
1578079	cable tie, 7.5*300mm White	4-80	120	55
1578080	cable tie, 7.8*350mm Black	4-90	120	55
1578081	cable tie, 7.8*350mm White	4-90	120	55
1578082	cable tie, 7.6*370mm Black	4-98	120	55
1578083	cable tie, 7.6*370mm White	4-98	120	55
1578084	cable tie, 7.6*400mm Black	4-105	120	55
1578085	cable tie, 7.6*400mm White	4-105	120	55
1578086	cable tie, 7.8*450mm Black	4-110	175	79.4
1578087	cable tie, 7.8*450mm White	4-110	175	79.4
1578088	cable tie, 7.8*500mm Black	4-150	175	79.4
1578089	cable tie, 7.8*500mm White	4-150	175	79.4
1578090	cable tie, 8.0*450mm Black	4-110	175	79.4
1578091	cable tie, 8.0*450mm White	4-110	175	79.4
1578092	cable tie, 8.8*500mm Black	8-150	175	79.4
1578093	cable tie, 8.8*500mm White	8-150	175	79.4
1578094	cable tie, 8.8*600mm Black	8-170	175	79.4
1578095	cable tie, 8.8*600mm White	8-170	175	79.4
1578096	cable tie, 8.8*650mm Black	8-190	175	79.4
1578097	cable tie, 8.8*650mm White	8-190	175	79.4
1578098	cable tie, 8.8*700mm Black	10-205	175	79.4
1578099	cable tie, 8.8*700mm White	10-205	175	79.4
1578100	cable tie, 8.8*800mm Black	10-230	175	79.4
1578101	cable tie, 8.8*800mm White	10-230	175	79.4
1578102	cable tie, 8.8*900mm Black	10-265	175	79.4
1578103	cable tie, 8.8*900mm White	10-265	175	79.4
1578104	cable tie, 8.8*1000mm Black	10-300	175	79.4
1578105	cable tie, 8.8*1000mm White	10-300	175	79.4

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau ([www.conrad.com](http://www.conrad.com)).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data represent the technical status at the time of printing. Changes in technology and equipment reserved.

© Copyright 2017 by Conrad Electronic SE.