


RoHS COMPLIANT



SPECIFICATIONS:

1. RATING: 11V AC 1A MAX
OR 12V DC 2A MAX.
2. INSULATION RESISTANCE:
50M OHM MIN AT 500V DC.
3. DIELECTRIC STRENGTH:
500V AC / 1 MINUTE.

	7.0φ BACK SHELL
	6.0φ BACK SHELL
X	5.0φ BACK SHELL (STANDARD)
	COVER DIM.

TABLE A

MATERIAL:

- A. COVER: PE+2L
- B. SHELL: ABS
- C. METAL SHIELD:
BRASS NICKEL PLATED
- D. HOUSING: NYLON66+GF
- E. CONTACT:
BRASS SILVER PLATED