



8	Terminals	Brass	Silver Ptd.	6
7	6P Housing	ABS		1
6	"T" Holder	Steel	Nickel Ptd.	1
5	Setscrew	Steel	Nickel Ptd.	1
4	Hook Button	Zn Alloy	Nickel Ptd.	1
3	Leaf Spring	Steel	Thermal Treatment	1
2	Strain Boot	PVC		1
1	Shield Cover	Zn Alloy	Nickel Ptd.	1

Specifications
rating : 100V AC 4A MAX
contact resistance : plus-30mΩ MAX; shell-50mΩ MAX
insulation resistance : MIN 100 MEGΩ @500V DC
voltage withstand : 250V AC R.M.S. for 1 minute