

SPECIFICATIONS

- Rating:** 100VAC 1A (max.)
12VDC 2A (max.)
- Dielectric withstanding voltage:**
500VAC, 60Hz for 1 minute
- Insulation resistance (initial):**
100M Ω (min.) at 500V DC
- Contact resistance (initial):**
30m Ω (max.) at AC 100mA (max.) 1 KHz
- Insertion & Extraction force:**
Initial : 4.5kgs (max.)
Extraction force: 0.9 to 3.0kgs

MATERIALS

- Insulator:** PBT(Black, UL94V-0)
 - Contact:** Phosphor bronze.
 - Metal Shell:** Copper alloy
- All materials must be RoHS compliant.

