

DIMENSIONS(MALE)

| SHELL SIZE | A | B | C | D | E |
|------------|----------------|----------------|----------------|----------------|----------------|
| | 0.010 0.25 | 0.005 0.13 | 0.015 0.38 | 0.010 0.25 | 0.015 0.38 |
| 9 | 0.666 16.92 | 0.984 24.99 | 1.213 30.81 | 0.759 19.28 | 0.426 10.82 |
| 15 | 0.994 25.25 | 1.312 33.32 | 1.541 39.14 | 1.083 27.51 | 0.426 10.82 |
| 25 | 1.534 38.96 | 1.852 47.04 | 2.088 53.04 | 1.625 41.28 | 0.426 10.82 |
| 37 | 2.182 55.42 | 2.5 63.5 | 2.729 69.32 | 2.272 57.71 | 0.429 10.9 |
| 50 | 2.079 52.81 | 2.406 61.1 | 2.635 66.93 | 2.178 55.32 | 0.429 10.9 |

